

Stainless Steel Belt Conveyor

Mfg:

Model:

Stock No. ERCS060.

Serial No.:

Stainless Steel Belt Conveyor. Link belt width: 2 ft. Maximum aperture/clearance above belt: 2 ft. 2-1/2 in. W x 5-1/2 in. H. Rod diameter: 0.175 in. Distance between rods: 0.6 in. Gap between rods: 1 ft. 11-1/4 in. L x 1/2 in. W. (4) Wheels for easy maneuverability. Baldor Industrial Motor, 1/2 hp, 208-230/460 V, 1.8-1.6/0.8 amps, 1725 rpm, 60 Hz, 3 phase. Hub City Drive, ratio: 30/1WR, 57.5 rpm (final). Conveyor infeed/exit height: 3 ft. 9 in. Overall dimensions: 15 ft. 6 in. L x 3 ft. 6 in. W x 4 ft. 3 in. H.

