

Aloe Vera Leaf Fillet Machine

Mfg:	Model:
Stock No. 75.GALO3	Serial No.

Aloe Vera Leaf Fillet Machine. Makes 1 in. wide cuts. Number of rotating blades: (6) 3 in. dia. Distance between blades: 1 in. Maximum leaf width: 6 in. Infeed conveyor belt width: 7 in. W. Discharge conveyor belt width: 7 in. W. Magnetek Electric Motor, 1/2 hp, 1725 rpm, 115/208-230 V, 9/3.5-3.6 amps, 60 Hz, single phase. Dayton Drive, ratio of 15.1, 115 rpm (final). Conveyor infeed/exit height: 36 in. Outlets: (1) 10 in. L x 12 in. W product discharge chute, (1) 33 in. L x 8 in. W bi-product discharge chute. Overall dimensions: 8 ft. 4 in. L x 2 ft. 4 in. W x 3 ft. 8 in. H.



