

## Arrowhead Conveyor Company Bottle Elevator

Mfg: Arrowhead Conveyor Company

Model: GRIPPER S-EL

Stock No. GM370.1

Serial No. \_\_\_\_\_

Arrowhead Conveyor Company Bottle Elevator. Model: GRIPPER S-EL. P.O: CSC 0109. S/O and Equip No: 076760SE. Line No: 301. Lines per chain: 238. Maximum opening width: 12 in. Sew-Eurodrive Motor (aperture), 3 hp, 1700 rpm, 230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. Sew-Eurodrive Variable Speed Reducer, 10.50 ratio, 44/217 rpm (min/max). Conveyor infeed height: 3 ft. Conveyor exit height: 11 ft. Overall dimensions: 8 ft. 10 in. L x 3 ft. 5 in. L x 11 ft. 4 in. H.





**CONVEYOR CO., INC.**  
 OSHKOSH, WISCONSIN

GRIPPER   DOUBLE

PURCHASE ORDER  080 0109

SHOP ORDER  076780SE

EQUIP. NO.  076780SE

ME NO.  301

LINKS PER CHAIN  236

**SEW-EURODRIVE, INC.** US

Type  3AFF 62D23DT1100LS4

S.O.  350015 156 . 94 . 94 . 001

In  430/2273 rpm Out  44/217

Torque  630

Ratio  10.50 Service Factor  1.0

Mounting Position  H5A

Lubrication  MOBILGEAR 686 0 °C/10

Product See Operating Instr. Min Amb