

Chester Jensen/York Plate Heat Exchanger

Mfg: Chester Jensen/York

Model: HT-54

Stock No. GOB5451.4

Serial No. 9513594

Chester Jensen/York Plate Heat Exchanger. Model: HT-54, S/N: 9513594. 304 Stainless steel plates: (81). Heat transfer surface area: Approx. 105 sq. ft. Design pressure: max 40 psig. Fixed end ports: (4) 2 in. Movable end ports: (4) 2 in. Divider 1 ports: (4) 1-1/2 in. Divider 2 ports: (4) 1-1/2 in. Overall dimensions: 60 in. L x 24 in. W x 54 in. H.

