

Chester Jensen/York Plate Heat Exchanger

Mfg: Chester Jensen/York

Model: HT-48

Stock No. 75.GOB5481.5

Serial No. 1257584

Chester Jensen/York Plate Heat Exchanger. Model: HT-48, S/N: 1257584. 304 Stainless steel plates: (101). Heat transfer surface area: Approx. 132 sq. ft. Design pressure max: 40 psig. Fixed end ports: (4) 2 in. Movable end ports: (4) 2 in. Overall dimensions: 60 in. L x 24 in. W x 54 in. H.

