

MODEL	ROWS DEEP	FPI	CAPACITY DATA BTUH/°TD		CFM	SURFACE (FT <sup>2</sup> )	NO. FANS	MOTOR HP	COIL VOLUME (FT <sup>3</sup> )	APPROX. SHIPPING WEIGHT
			LR	DX						
CO 118	4	4	1,550	1,330	2,540	304	1	1/4	.6	650
	6	4	2,010	1,730	2,500	457			.9	750
	8	4	2,250	1,940	2,440	609			1.2	840
	4	6	1,960	1,690	2,490	444			.6	755
	6	6	2,290	1,970	2,400	666			.9	905
	8	6	2,430	2,090	2,320	888			1.2	1,050
CO 218	4	4	2,930	2,520	4,990	554	2	1/4	1.0	895
	6	4	3,770	3,240	4,870	831			1.5	1,050
	8	4	4,300	3,700	4,750	1,109			2.0	1,210
	4	6	3,730	3,210	4,910	808			1.0	1,085
	6	6	4,370	3,760	4,700	1,211			1.5	1,335
	8	6	4,660	4,010	4,520	1,616			2.0	1,590
CO 318	4	4	3,860	3,320	7,120	673	3	1/4	1.1	965
	6	4	5,040	4,330	6,900	1,010			1.7	1,250
	8	4	5,650	4,860	6,560	1,347			2.3	1,560
	4	6	4,880	4,200	6,980	981			1.1	1,195
	6	6	5,830	5,010	6,580	1,472			1.7	1,600
	8	6	6,200	5,330	6,210	1,962			2.3	2,020
CO 418	4	4	5,010	4,310	9,360	863	4	1/4	1.5	1,105
	6	4	6,540	5,620	9,100	1,295			2.2	1,550
	8	4	7,400	6,360	8,600	1,727			2.9	1,950
	4	6	6,340	5,450	9,190	1,257			1.5	1,465
	6	6	7,570	6,510	8,650	1,886			2.2	1,995
	8	6	8,080	6,950	8,130	2,514			2.9	2,540
CO 324	4	4	7,350	6,320	13,340	1,296	3	1/3	2.2	1,520
	6	4	9,550	8,040	12,550	1,943			3.2	1,900
	8	4	10,500	9,030	12,050	2,591			4.3	2,220
	4	6	9,270	7,970	13,040	1,887			2.2	1,965
	6	6	11,000	9,460	12,290	2,830			3.2	2,565
	8	6	11,650	10,020	11,580	3,774			4.3	3,165