

## Alfa Laval Plate Heat Exchanger

Mfg: Alfa Laval

Model: H10-FMC

Stock No. HDAF532.42a

Serial No. 4237

Alfa Laval Plate Heat Exchanger. Model: H10-FMC. S/N: 4237. Stainless steel plates: (110). Heat transfer surface area: approx. 675 sq. ft. Maximum working pressure: 145 psig. Maximum working temperature: 285 °F. Fixed end ports: (1) 3 in. dia. ACME inlet, (1) 3 in. dia. ACME outlet. Divider: (1) 3 in. dia. ACME inlet, (2) 3 in. dia. ACME outlet. Movable end ports: (1) 3 in. dia. ACME inlet, (1) 3 in. dia. ACME outlet. Overall dimensions: 9 ft. L x 34-1/2 in. W x 8 ft. 4 in. H.

