

Crepaco Plate Heat Exchanger

Mfg: Crepaco

Model: CR5

Stock No. HDAF957.62

Serial No. C-1163

Crepaco Plate Heat Exchanger. Model: CR5. S/N: C-1163. Number of stainless steel plates: 214. Heat transfer surface area: approx. 1337 sq. ft. Fixed end ports: (4) 4 in. dia. S-Line (4) Divider Inlets: (8) 2 in dia. NPT fittings (male). Outlets: (7) 2 in. dia. NPT fittings (male). Terminal ports: (4) 4 in. dia. S-Line. Vickers Vane Pump, Reliance Motor, 5 hp, 1730 rpm, 230/460 V, 14/7 amps, 60 Hz, 3 phase. Inlet/outlets: 1 in. dia. NPT (female) port. Overall dimensions: 11 ft. 8 in. L x 36 in. W x 8 ft. 6-1/2 in. H.



