

## 1990 APV Centrifugal Pump

Mfg: APV

Model: 4V2



Stock No: HDDF271.1

Serial No: G-2534-90

1990 APV Centrifugal Pump. Model: 4V2. S/N: G-2534-90. Pump capacity: 65 gpm. Impeller: 3-13/16 in. diameter. Seal option: APV Type 1 single mechanical. Reliance Electric Motor, 1.5 hp, 1750 rpm, 208-230/460/575 V, 60 Hz, 3 phase. The V2 series is designed for pumping low to medium viscosity liquids. Stainless steel head components. Optimum design for sanitary service. Pump inlet/outlet: 1 1/2 in. 'S' line. Overall dimensions: 1 ft. 7 in. L x 10 in. W x 8 in. H.







EASILY CLEAN A-C MOTOR						
FR FC145T	TYPE P	PH 3				
RPM	VOLTS	AMPS	HZ	SF		
1725	208-230	*	60	1.0		
/460/575						
NEMA 40						
NEMA 3102A B COPR F						
UL EEC CERTIFIED STD 29						
1/2 3/2.2						
7-50V 50Hz						
ELECTRIC COMPANY						
LEVELAND, OHIO 44117						
PLANT M						
144 FILE E 546						
MADE IN U.S.A.						