

APV Crepaco Stainless Steel Vibratory Feeder

Mfg: APV Crepaco

Model: V-2

Stock No: HDDG391B.1

Serial No: V2-N-1666

APV Crepaco Stainless Steel Vibratory Feeder. Model: V-2. S/N: V2-N-1666. Electrical requirements: 115 V single phase. The APV Crepaco V-2 Dry Ingredient Vibratory Feeder continuously meters dry ingredients ranging in capacity of a few ounces (grams) to approximately 30 lbs per minute and may be varied during operation to match changing production requirements. Applications include: flake coconut, raisins, peanuts, marshmallows, nuts, seeds, cut dry fruit, granular salt, dry soup, condiments and almost anything else that is a dry granular ingredient. The V-2 is compact and portable and equipped with rolling castors. Vibrating pan dimensions: 22 in. L x 5 in. W x 2 through 3 in. H. Product chute dimensions: 1 ft. 8-1/4 in. top L x 1 ft. 2 in. top W straight wall: 1 ft. 2 in. 4-1/4 in. bottom L x 3-1/2 bottom W. Overall dimensions: 2 ft. 8 in. L x 1 ft. 9 in. W x 4 ft. 6 in. H.



