

Allen-Bradley Variable Frequency AC Drive

Mfg: Allen-Bradley

Model: 1336

Stock No. HDDP065.a

Serial No. MF01AD64

(4) Allen-Bradley Variable Frequency AC Drive. Model: 1336. S/N: MF01AD64. Provides constant torque. Input: 9.2 Amps, 50/60 Hz, 380/415/460 V, 6.1/6.6/7.3 KVA. Output: 9.6 Amps, 0-250 Hz, 380/415/460 Volts, 6.3 /6.9/7.6 KVA. Overall dimensions: 11 in. L x 9 in. W x 19 in. H.

