

Assorted Motors

| | |
|-----------------------------|-------------------|
| Mfg: | Model: |
| Stock No. HDNP916.11 | Serial No. |

Baldor Motor, 1/2 hp, 1,725 rpm, 230/460 volt, 2/1 amps, 60 hz, 3 phase, 56C frame.



Baldor Motor, 3/4 hp, 1,725 rpm, 208-230/460 volt, 3.2-3/1.5 amps, 60 hz, 3 phase, 56 frame.



(2 motors) Dayton, 1/2 hp, 3450/2850 rpm, 208-220/440 volt, 2.2-2.3/1.15 amps, 60/50 hz, 3 ph, D56C frame.



Dayton, 1 hp, 1,725 rpm, 230/460 volt, 3.6/1.8 amps, 60 hz, 3 phase, XG56H Frame.



Dayton, 1-½ hp, 3,450 rpm, 115/230 volt, 19.0/9.5 amps, 60 hz, 1 phase, 56J frame.



Dayton, 1-½ hp, 3,450/2,850 rpm, 208-220/440 volt, 4.4-4.2/2.1 amps, 60/50 hz, 3 phase, G56C.



Dayton, 3 hp, 1,725 rpm, 230/460 volt, 9.4/4.7 amps, 60 hz, 3 phase, L56C frame.



Emerson, 3/4 hp, 1,750 rpm, 180 volt, 4 amp (DC), 56C frame.



Leeson, 1/2 hp, 1,750 rpm, 90 volt, 5amp (DC), VS 56C frame.



Reliance, 3/4 hp, 1,725 rpm, 208-230/460 volt, 2.8-3.0/1.5 amps, 60 hz, 3 phase, FB 56 C frame.



Reliance, 3/4 hp, 1,725 rpm, 230/460 volt, 4.1/2.05 amps, 60 hz, 3 phase, M56C frame.



US Electrical motor, 1/3 hp, 1,745 rpm, 208-230/460 volt, 1.3-1.2/0.6 amps, 60 hz, 3 phase, 56C frame.



US Electrical motor, 1/2 hp, 1,745 rpm, 208-230/460 volt, 1.9-1.84/0.92 amps, 60 hz, 3 phase, 56C frame.



US Electrical motor, 2 hp, 3,460 rpm, 230/460 volt, 5.4/2.7 amps, 60 hz, 3 phase, 56C frame.

