

## Assorted Motors

Mfg:

Model:

Stock No. HDNP917.3a

Serial No.

Baldor Motor, 1/3 Hp, 1,750 rpm, 90-100/50 volt (DC), 3.4-0.4/0.8 amps, 56 C frame.



Lincoln, 1/3 hp, 1,740-1,750 rpm, 208-230/460 volt, 1.1-1.3/0.7 amps, 60 hz, 3 phase. 56C frame.



2 Baldor Motors, 1/2 hp, 3,450 rpm, 230/460 volt, 2.4/1.2 amps, 60 hz, 3 phase, 56J frame.



Dayton Motor, 1,725/1,425 rpm, 3.4hp, 230/460 volt, 2.4/1.2 amps, 60/50 hz, 3 phase, G56 Frame.



US Electrical Motors, 1 hp, 1,750 rpm, 208-230/460 volt, 36-3.6/1.8 amps, 60 hz, 3 phase, 143 TC frame.



Baldor Motor, 1 hp, 1,750 rpm, 230/460 volt, 4.2/2.1 amps, 60 hz, 3 phase, 145 TC frame.



US Electrical Motors, 2 hp, 3,450 rpm, 208-230/460 volt, 6.0-5.3/2.7 amps, 60 hz, 3 phase, 56C frame.



Baldor Motor, 3 hp, 1,750 rpm, 460 volt, 4.1 amps, 60 hz, 3 phase, 182 TZ.

