

## Assorted Motors

Mfg:

Model:

Stock No. HDNP918.4

Serial No.

Baldor motor, 1-½ hp, 1,740 rpm, 230/460 volt, 4.2 amps, 60 hz, 3 phase, 145 TC Frame.



4 Lincoln Motors, 2 hp, 1,160 rpm, 230/460 volt, 7.1/3.55 amps, 60 hz, 3 phase, 184 T Frame.



Lincoln motor, 2 hp, 1,690-1,715 rpm, 208-230/460 volt, 6.2-6.0/3.0 amps, 60 hz, 3 phase, 145 TC Frame.



Lincoln motor, 3 hp, 1,745-1,755 rpm, 208-230/460 volt, 8.7-8.3/4.1 amps, 60 hz, 3 phase, 182 T.



Reliance motor, 3 hp, 1,755 rpm, 230/460 volt, 7.6/3.8 amps, 60 hz, 3 phase, 180 TC

