

1991 FES Kobe Screw Compressor Package - 100 HP

Mfg: FES Kobe

Model: 64

Stock No: HDPW954.45

Serial No: 91-9505-1301-02

1991 FES Kobe Screw Compressor Package. Model 64. S/N and FES contract: 91-9505-1301-02. Capacity at +20 °F is approximate 74 tons or at -20 °F suction about 33 tons capacity. Ram Motor, 100 hp, 3532 rpm, 230/460 V, 230/115 amps, 60 Hz, 3 phase. Tuthill Rotary Pump, Model: 1311007103. Franklin Electric Motor, 1-1/2 hp, 208/230 V, 4.0/2.0 FLA, 4.5/2.25 SFA, 60/50 Hz, 3 phase. FES Micro Master Control Panel, power supply: 120 V, 15 FLA, 60 Hz, single phase. Pressure vessel: Nat'l Bd: 5268. MAWP: 300 psi. @ 200 °F. MDMT: -20 °F @ 300 psi. Inlets: (1) 3 in. dia. refrigerant suction port. Outlets: (1) 1/2 in. dia port, (1) 1 in. dia. port, (1) 2 in. dia. refrigerant discharge port. Overall dimensions: 8 ft. L X 3 ft. 6 in. W X 5 ft. 9 in. H. Compressor run time: 33755 hrs.(ACN300).





