

Cherry-Burrell 2-Barrel Vogt Freezer

Mfg: Cherry-Burrell

Model: V-603

Stock No. HDRG071.34a

Serial No. 4907

Cherry-Burrell 2-Barrel Vogt Freezer. Model: V-603. S/N: 4907. (2) U.S. Motors, 15 hp, 1500/1800 rpm, 208-220/440 V, 22/44-20/40 amps, 50/60 Hz, 3 phase. Driver pulley: 3 in. Driven pulley: 17 in. Pulley ratio: 0.176. Rotor final speed: 317.6 rpm. (2) Waukesha Positive Displacement Pumps, Model: 22IC2, S/Ns: 310173 02 and 311383 02. (2) Sew-Eurodrive Motors, 3 hp, 226-2257 rpm, 230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Reducer, 5.64 ratio, 40-400 rpm (final). (2) Cherry-Burrell Accumulator Tanks, S/Ns: CR5247 and CR5248, F.P: 19799, MAWP: 200 psi @ 400°F. (2) TB Woods Remote Station Speed Controllers. Inlets: (2) 3/4 in. dia. hot gas feed ports, (2) 1-1/2 in. dia. S-line fittings (pumps), (2) 1-1/2 in. dia. Q-line fittings (barrels). Outlets: (2) 1 in. dia. Q-line fittings (barrels), (1) 1-1/4 in. pressure relief port, (2) 1-1/2 in. dia. S-line fittings (pumps), (1) 2 in. dia. refrigerant suction port. Overall dimensions: 6 ft. 6-1/2 in. L x 6 ft. 4 in. W x 9 ft. 1 in. H.



















