

Purity Insulated Stainless Steel Rectangular Processor Tank- 2200 Gallon

Mfg: Purity

Model:

Stock No. HDTD095.2a

Serial No. 223

Purity Insulated Stainless Steel Rectangular Processor Tank- 2200 Gallon. S/N: 223. Inside dimensions: 9 ft. 6 in. L x 48 in. W x 95 in. H. Tank features (7) 1-1/2 in. dia. x 8 ft. L internal heating tubes, dual sprayballs, (1) 5-1/2 in. dia. sight glass, and a 20 in. W x 16 in. H manway. Heating surface area: approx. 21 sq. ft. Vertical agitator has two 22 in. dia. blades. Master Gearmotor, 3/4 hp, 1725/1425 rpm, 48/10 rpm (final), 2.3/1.15 amps, 60/50 Hz, 3 phase. Inlets: (1) 1 in. dia. NPT (heating tubes), (1) 1-1/2 in. dia. S-line sprayballs, (1) 2 in. dia. S-line fitting, (1) 4 in. dia. S-line fitting, (1) 3/4 in. dia. thermowell with thermometer. Outlets: (1) 1 in. dia. NPT (male, heating tubes), (1) 2 in threaded bypass valve tank. Overall dimensions: 11 ft. 3 in. L x 55 in. W x 10 ft. H.



