

Vilter 4416 16-Cylinder Reciprocating Compressor

Mfg: Vilter / Emerson Climate

Model: 440 Series

Stock No.: HFLT01.30

Serial No.: 20972

Vilter 4416 16-Cylinder Reciprocating Compressor. Refrigerant: AMMO (ammonia, R717). Serial: 20972. Low/High Side Design pressure: 162 / 320 PSIG. Order: D-79078-3. Size: A11K-4416C. Voltage: 115V. Number of cylinders: 16. Nominal tonnage rating: 227.4 TR / 144 BHP at +20F suction / 95F condensing temp. Max RPM: 1200. Displacement: 619 M3/hr (364.33 CFM). Ports: 6 in. suction, (2) 3 in. discharge.





REFRIGERATION
AIR CONDITIONING

Vilter

MANUFACTURING CORP
MILWAUKEE, WIS.
REFRIGERANT

AMMO

SERIAL NO.

HIGH SIDE DESIGN PRESS. PSIG.

20972

320

ORDER NO.

LOW SIDE DESIGN PRESS. PSIG.

D-78078-3

162

SIZE

VOLTAGE

110/115/160

115