

**SWECO Stainless Steel Separator – 45 in.**

**Mfg: SWECO**

**Model: A-1D**


**Stock No: HNDC481**

**Serial No: 284**

SWECO Stainless Steel Separator. Model A-1D. Serial No: 284. (2) 45 in. diameter product / screen contact surfaces. Motor: 1 hp, 220V, 3 phase. Sweco separators offer maximum throughput and screening efficiency to many types products by accomplished vibration over a screen cloth with varieties of mesh sizes to fit specific applications. Products and actions addressed include: sizing for dry products to include: sugars, spices, feeds, and abrasives; “scalping” to remove unwanted, oversized particles to include metal bits, blood and bone material; gravity filtering and product recovery from slurries such as ceramics; and waste water cleanup which could include brewery waste, laundry waste, or many other effluent applications. This unit was in prior service with Crane Plumbing in their porcelain processing line. (2) 8 in. discharge spouts. Top level discharge opening 14 in. L x 6 in. H. Bottom level discharge opening 11 in. L x 3.5 in. H. Overall dimensions: 4 ft. 10 in. L x 3 ft. 11-1/2 in. W x 3 ft. 3 in. H.







8222  
SWECO

# SWECO SEPARATOR

PATENT NO. 2,284,671

MODEL A-1D SERIAL NO. 284  
RPM 1200 HP 1 VOLTS 220 PHASE 3

SOUTHWESTERN ENGINEERING CO., LOS ANGELES, CA