

Frick PRR Refrigerant Recirculator - 3 ft. Dia. x 11 ft. 6 in.

Mfg: Frick

Model:

Stock No. IME2401

Serial No.

Frick PRR Refrigerant Recirculator - 3 ft. Dia. x 11 ft. 6 in. Nat'l Bd: 52125. MAWP: 150 psig @ -20° F to 200° F. Material SA: 515.GR70, T.S. 70000. Shell chamber thickness: 0.250 in. Head thickness: 0.250 in. Head radius: 2:1. Tank dimensions: 11 ft. 6 in. L x 3 ft. dia. (2) Blackmer Pumps, Model: RAL2, S/N's: 64338 and 64477. (2) Marathon Electric Motors, 2 hp, 1735 rpm, 208-230/460 V, 6.0/3.0 FLA, 60 Hz, 3 phase. Overall dimensions: 12 ft. 6 in. L x 91 in. W x 10 ft. 3 in. H.



