

Pneumatic Scale Corp. 8-Head Capper with Rotating Cap Sorter

Mfg: Pneumatic Scale Corp.

Model: Pneumacap 3338

Stock No. JPSE823.

Serial No. 21438

Pneumatic Scale Corporation Pneumacap-Series 8-Head Capper with Rotating Cap Sorter. Model: Pneumacap 3338. S/N: 21438. Nominal capacity: 240 cpm. Maximum Container diameter: 4 ½ in. Maximum Container height: 12 in. Chute installed will place 30mm x 12mm (1.18 in. dia. x 1.5 in. H.) caps. Also has change out chute 30mm x 35 mm (1.176 in. dia. x 1.391 in. H). Conveyor dimensions: 4 ½ in w x 43 in. L. Conveyor infeed/exit height: 37 in. General Electric Motor, ¼ hp, 1725 rpm, 575 V, 0.42 amps, 60 Hz, 3 phase. Overall dimensions: 9 ft. 1 in. L x 4 ft. 3 in. W x 8 ft. H.











