

APV Crepaco Positive Displacement Pump

Mfg: APV Crepaco

Model:

Stock No: KAAM0220B

Serial No:

APV Crepaco Positive Displacement Pump. Baldor industrial motor, 15 hp, 1760 rpm, 208-230/460 V, 40-37/18.5 amps, 60 Hz, 3 phase. Speed reducer, 5.0:1 ratio, input: 1750 rpm, output: 350 rpm, torque capacity: 6,315 in./lbs. Inlets: (1) 9 in. L x 6-1/2 in. W infeed. Outlets: (1) 4 in. dia. ACME fitting. Overall dimensions: 5 ft. 8 in. L x 1 ft. 10 in. W x 2 ft. 11 in. H.





