Sabroe 8-Cylinder Reciprocating Compressor	
Mfg: Sabroe	Model: SMC108L
Stock No: KMPN02	Serial No:

Sabroe 8-Cylinder Reciprocating Compressor. Model: SMC108L. Compressor only, no motor or base is included. Bore x Stroke: 100mm x 100mm. Max RPM: 1500. Swept volume at max RPM: 565 cubic meters / hour. Nominal Capacities(R717): 335kW at -10/+35C high stage; 531kW at 0/+35C high stage; 93kW at -40/-10C booster. Nominal Capacities (R404): 416kw at 0/+35C high stage; 270kW at -10/+35C high stage. Dimensions: 75 in. to 100 in. long x 39.5 in. wide x 44.5 in. high. Weight: 2,200 lbs. Sound pressure level 83 dB(A). Sabroe Products is part of Johnson Controls.



