

## 1994 Waukesha 130 Positive Displacement Pump

Mfg: Waukesha

Model: 130

Stock No. KVST001.

Serial No. 142918

1994 Waukesha Positive Displacement Pump. Model: 130. S/N: 142918. Pumping capacity: 72 gpm @ 25psi. Nominal Capacity: 150 gpm. Displacement per Revolution: 0.254 gallons. Maximum speed: 600 rpm. Seal option: Double O-ring with flush, buna elastomers. US Electric Motor, 15 hp, 1765 rpm, 230/460 V, 39.2/19.6 amps, 60 Hz, 3 phase. Motors series 2000 Gear Drive, ratio: 5.6, torque 5275, 315 rpm (final). Waukesha sanitary pumps feature easy cleaning and disassembly. Typical products handled by Waukesha pumps include products from bakery, beverage, canning, confectionary, cosmetics, dairy, meat packaging, and pharmaceutical industries. Inlets/outlets: (2) 3 in. dia. S-line fittings. Overall dimensions: 4 ft. 10 in. L x 1 ft. 9 in. W x 2 ft. H.







**ENCLOSED HIGH EFFICIENCY MOTOR**

|                     |                             |          |                            |               |          |     |       |
|---------------------|-----------------------------|----------|----------------------------|---------------|----------|-----|-------|
| IP 15               | PH 3 HZ 60                  | RPM 1765 | CODE G                     | NEMA DESIGN B | SIZE 200 | 171 | BB, S |
| FRAME 254TC         | TYPE UT TE                  | SF 1.25  | DUTY: MAX. 40°C CONT. AMB. |               |          |     |       |
| VOLTS 230 460       | I.D. A981AW08W179RO42F      |          | INSUL. F CLASS             |               |          |     |       |
| P.L. AMPS 39.2 19.6 | SHAFT END BRG. 6309-2Z-J/C3 |          |                            |               |          |     |       |
| L.L. AMPS 48.0 24.0 | OPP. END BRG. 6207-2Z-J/C3  |          |                            |               |          |     |       |

AT 1.0 S.F. CLASS F RISE USABLE 208V AT 43.3 AMPS OR 190/380V 46.0/23.0 AMPS  
 ALTERNATE 40°C. AMB. 1.15 S.F. CLASS B RISE OR 50°C. AMB. 1.15 S.F. CLASS F RISE

**U.S. ELECTRICAL MOTORS**  
 DIVISION OF EMERSON ELECTRIC CO.  
 MILFORD, CONNECTICUT

STAR-Y-CONNECTION  
 480 VOLTS  
 230 VOLTS

**Waukesha Fluid Handling**  
 A United Dominion Company

MODEL 02-08

SERIAL NO. 14231  
 MODEL 130

**READ AND UNDERSTAND OPERATION AND MAINTENANCE MANUAL BEFORE OPERATION.**

DELAWARE, WI U.S.A.

MOTORS

SERIES 2000

RATIO 6

INPUT 1.976 RPM

OUTPUT TORQUE 5275 IN LBS

AT.# CBN2501983-5.611250

SER.# CB 2.0004299-Y02

ASSEMBLED IN U.S.A.

39684