

Reliance Electric Motor - 7-1/2 HP

Mfg: Reliance

Model:

Stock No: KWBF750Q

Serial No:

Reliance Electric Motor. Id No. P21F11 PN. Motor specifications: 7-1/2 hp, 1745 rpm, 230/460 V, 19.0/9.5 amps, 60 Hz, 3 phase. Frame: 213T. Nema design: B. Type: P. Shaft diameter: 1-1/2 in. Overall dimensions: 1 ft. 1 in. L x 10 in. W x 9 in. H.



