

Reco Vertical Ammonia Recirculator Package – 48 in. Dia. x 10 ft. H

Mfg: Reco

Model:

Stock No: KWBF917

Serial No: 19025-260A

Reco Vertical Ammonia Recirculator Package. S/N: 19025-260A. National Board: 7695. Refrigerant: R-717 (Ammonia). Approximate capacity: 1,000 gallons. MAWP: 150 psi at 300°F. MDMT: -20°F at 150 PSI. Inside straight wall: 4 ft. dia. x 10 ft. H. Radius: 2:1 elliptical ends. Inlets: (1) 1 in. dia. port, (1) 2 in. dia. port, (1) 6 in. dia. port. Outlets: (3) 6 in. dia. port, (1) 3/4 in. dia. port, (1) 2 in. dia. port. Reco oil pot, MAWP: 300 psi at 300°F, MDMT: -20°F at 300 psi. Cornell ammonia pump, Model: 3CB-F16, S/N: 72411. Flow rate for new pump is 470 gpm with required horsepower and pressure. Impeller diameter: 15.22 in. Inlet: 6 in. suction. Outlet: 3 in. discharge. Overall dimensions: 5 ft. 5in. L x 5 ft. 6 in. W x 15 ft. 3 in. H.









