

2003 Unused Copeland Digital Scroll Compressor - 6HP

Mfg: Copeland

Model: ZFD18KVE-TF5-251

Stock No.: LYNT006

Serial No.: 03K75725G

2003 Unused Copeland Digital Scroll Compressor – 6 HP. Model: ZFD18KVE-TF5-251. S/N: 03K75725G. Capacity rating for R-404: 5.2 tons. 60 Hz & 50 Hz, 200-230 V & 200-220 V, 156 LRA, 21 I, 20.58 volume & 17.05 volume, 3500 rpm & 2900 rpm, 417.70 psi (28.8 bar). Scroll parts/systems: discharge check valve, dynamic discharge valve, pressure relief valve, flotation seal, fixed scroll, orbiting scroll, oil service valve, sight glass, liquid injection, DU bearing, internal thermal protector, lubrication, mesh filter, magnetic trap, temperature sensor, internal motor protection. Scroll dimensions: 7 in. diameter x 18 in. H. Additional parts/equipment: (3) Oil level control systems, (2) valves: 1/2 in. pipe, Sight glass: 2-3/8 diameter, valve: 3 in. threaded male, valve: 1 in. pipe, valve: 1-3/4 in. pipe, (2) Sporlan relief valves. Overall dimensions: 15 diameter x 20 in. H.(ACN18).



