

Siemens Electric Induction Motor – 50 HP

Mfg: Siemens

Model:

Stock No: MBNC018.3a

Serial No:

Siemens Electric Induction Motor. Motor specifications: 50 hp, 1765 rpm, 230/460 V, 120.4/60.2 amps, 60 Hz. Frame: 326TS, Insulation Class: F. Design: B. Code: G. Shaft diameter: 1-5/8 in. Shaft length: 4 in. Overall dimensions: 30 in. L x 20-1/2 in. W x 17-1/2 in. H.(ACN35).





SIEMENS

QUALITY INDUCTION MOTOR

ORD. NO.	1LA03264FC21	195		
TYPE	R67	FRAM. 326TC		
H.P.	50	1.15		
AMPS	120.4/60.2	VOL. 230/460		
R.P.M.	1765	HERTZ 60		
DUTY	CONT. 40	AMB		
CLASS	F	B	C	91.7
INSUL	60BC03JPP3	506C02J2P3		
ENV				

Siemens Electric Corporation, All rights reserved.