

1990 APV Crepaco 5-Piston Homogenizer

Mfg: APV Crepaco



Model: 5DD425




Stock No: MDBC042.45




Serial No: 5DD425-3060


1990 APV Crepaco 5-Piston Homogenizer. Model: 5DD425. S/N: 3060. Rated capacity: 1,500 GPH at 1,800 psi. Single stage manual valve assembly. Plunger diameter: 1.249 in. Turbo flow and poppet valves. Spare parts included. Westinghouse electric motor, 30 hp, 1180 rpm, 230/460 V, 72.6/36.3 amps, 60 Hz, 3 phase. Motor pulley diameter: 6-1/2 in. Gear pulley diameter: 32 in. Ratio: 4.92. Final rpm: 240. Inlet: (1) 3 in. dia. ACME fitting. Outlet: 2 in. dia. I-Line fitting. Overall dimensions: 5 ft. 10 in. L x 4 ft. 2 in. W x 6 ft. H.











Westinghouse

Cat #		Rev.	Iss.
HP	3061	780P	Mod
3 Phase	60		
Wiring	306P42160	8	
Wiring	306P42160	40	
Sum	1140	1.15	
Wiring	306P421601		
Wiring	306P420801		
Wiring	306P421607	70P	