

APV/Crepaco Centrifugal Pump

Mfg: APV/Crepaco

Model: 6V2

Stock No.: MDBC083.2

Serial No.: G-2023-90

Crepaco Centrifugal pump. Model: 6V2. S/N: G-2023-90. Flow rate for new pump is 100 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 4-1/2 in. Electric Motors Unlimited motor, 3/1.5 hp, 3600/1800 rpm, 460 V, 3.9/3.2 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. ACME fitting. Outlet: (1) 1-1/2 in. ACME fitting. Overall dimensions: 1 ft. 10-1/2 in. L x 1 ft. W x 10 in. H. (ACN25)





INSPECTED OR MODIFIED BY:			
ELECTRIC MOTORS UNLIMITED/MADISON, WI			
DATE	HP	VOLTS	CONN.

PH	HZ	S.F.	RPM	AMPS