

# RVS Ammonia Surge Drum - 9 Gallon

Mfg: RVS

Model:

Stock No.: MDBC261C

Serial No.: 87077

RVS Ammonia Surge Drum. S/N: 87077. Nat'l Bd: 874. Approximate capacity: 9 gallon. Inside straight wall dimensions: 9-1/2 in. dia. x 2 ft. 4 in. L. Refrigerant: R-717. MAWP: 300 PSI @ 350° F. MDMT: -20° F @ 300 PSI. Inlets/outlets: (2) 3 in. dia. ports. Overall dimensions: 4 ft. 3 in. L x 2 ft. 5 in. W x 1 ft. 11 in. H.



	NAT'L BD.	874
	CERTIFIED BY	
	REFRIG. VALVES & SYSTEMS	
	MAWP	300 PSI AT 350° F
	SERIAL NO.	87077
	YEAR BUILT	1937
20	°F	MIN. ALLOW. WORK TEMP.
300	PSI	MAX. AT MIN. TEMP. UCS-66