

Lincoln A.C. Motor 125hp

Mfg: Lincoln

Model:

Stock No: MDBC264B

Serial No: 524882

Lincoln electric motor: 125 hp. Motor specifications: Frame 445-U, Phase 3, Volts 460, Type DG, NEMA Code F, NEMA Design B. Lincoln Code 1298-A1-PW, Hz.60, RPM 1770, Amps 144, Shaft diameter 3in. Overall dimensions L 3ft. 4in. x W 2ft. 7in. x H 2ft. 4in. (BB)



