

## Sperry Plate Filter Press

Mfg: Sperry

Model:

Stock No. MST001.4

Serial No.

Sperry Plate Filter Press. Filter press consists of (45) 24 in. x 24 in. Polipropileno press plates. (180 sq. ft.) and (23) 3/4 in. dia. valves. Leeson Motor, 1 hp, 4000 rpm, 115 V, 10 amps. Power Team Hydraulic Pump, Model: A, S/N: 1707X31188, Part No: PE304-2. Pressure: 10,000 psi/700 bar max. Inlets: (1) 3/4 in. dia. threaded MPT. Outlets: (1) 1/2 in. dia. barb fitting. Overall dimensions: 10 ft. L x 51 in. W x 52 in. H.



