

## Onan GenSet Natural Gas Powered Generator

Mfg: Onan



Model: 35FK



Stock No: NOI1306

Serial No: D950574624

Onan GenSet Generator. Model: 35FK. Serial No: D950574624. Spec: 75256C. Hours: 463. Ford engine. Model: CSG-6491-6005-A. S/N: 03549 B-27-RC. S.O. Options: 0034F. Model Code: NFA-0034-NBB. Natural gas ASCO Regulator. Cat: 8215850. S/N: A179985. Rebuild Kit: 302432. Air Inert Gas: 25 psi. Volts 12 DC. Watts 14.9. Fuel Gas 25 psi. Overall dimensions: 5 ft. 11 in. L x 2 ft. 9 in. W x 4 ft. H.








Model No. 306-3486-06	
Modele	
Serial No.	Spec.
Serie	


**IMPORTANT!**  
 Model & Serial No. Required When Ordering Parts.  
 Modele & No. Serie Requis Pour Commander Des Pieces.

 1400 73rd Avenue N.E.  
 Minneapolis, MN 55432 U.S.A.

 Made in U.S.A. 99-2433

CURRENT RATING:	70 AMPS
VOLTAGE:	440/480 VAC
FREQUENCY:	50/60 HZ

 1400 73rd Avenue N.E.  
 Minneapolis, MN 55432 U.S.A.

 Made in U.S.A. 99-2433

CURRENT RATING:	70 AMPS
VOLTAGE:	440/480 VAC
FREQUENCY:	50/60 HZ
POLES:	3

Suitable for control of motors, elec. discharge lamps, tungsten filament lamps & electric heating equipment where the sum of the motor full-load ampere ratings and the ampere ratings of other loads do not exceed the ampere rating of the switch and the tungsten load does not exceed 30% of the switch rating.