Project Quantity Item#

Model Specified: CSI Section 11400

# Compact Undercounter Refrigerator Models/Self-Contained



Model UHT27-R

#### 27", 32", 48", 60 & 72" Wide Models



Stainless Exterio

27" One Door Refrigerator Hinged Left
27" One Door Refrigerator Hinged Right
32" One Door Refrigerator Hinged Left
32" One Door Refrigerator Hinged Left
32" One Door Refrigerator Hinged Right
48" Two Door Refrigerator Hinged Left/Right
60" Two Door Refrigerator Hinged Left/Right
72" Two Door Refrigerator Hinged Left/Right
UHT72-LR

Traulsen's durable, high performance, compact undercounter refrigerator models provide a high quality/high value alternative to the all too common commodity types in today's market.

Durable, built with stainless steel exteriors and anodized aluminum interiors, their heavy duty cabinet construction promises years of useful service. Truly front breathing, their design allows for "zero-clearance" installation. As a result they can be placed right up against the back wall and alongside other kitchen equipment, saving valuable floor space.

Additionally, they offer a wide range of optional accessories to choose from, and are ideal for use with many different type applications.

## **Standard Product Features**

- Stainless Steel Exterior Top, Sides & Doors
- · Anodized Aluminum Interior
- · Front Breathing Self-Contained Refrigeration System
- Environmentally Friendly R-134a Refrigerant
- Self-Closing Stainless Steel Doors With Stay Open Feature At 105 Degrees
- · Anodized Aluminum Interior Door Liner
- Interior Mounted Thermometer
- Two (2) Powder Coated Shelves Per Door, Mounted On Pilasters
- Automatic Non-Electric Condensate Evaporator
- Magnetic Snap-In EZ-Clean Door Gasket(s)
- 8' Cord & Plug Attached
- Set of Four (4) 4" High Casters (6 For 60" & 72" models)
- · Three Year Parts And Labor Warranty
- · Five Year Compressor Warranty

# Optional Accessory Kits\*

- CASTER 5SET4 (four 6" high casters for 27", 32" & 48" models)
- CASTER 5SET6 (six 6" high casters for 60" & 72" models)
- CASTER SET3IN (four 3-1/2" high casters for 27", 32" & 48" models)
- CASTER SET4 (six 3-1/2" high casters for 60" & 72" models)
- CASTER SET2IN (four 2-1/2" high casters for 27" & 32" models)
- CASTER 2SET4 (four 2-3/4" high casters for 48" models)
- CASTER 2SET6 (six 2-3/4" high casters for 60" & 72" models)
- SHELF CPW1 (additional shelf for all 27" models)
- SHELF CPW2 (additional shelf for all 32" models)
- SHELF48 UPPER (upper shelf for all 48" models)
- SHELF48 LOWER (lower shelf for all 48" models)
- SHELF60 UPPER (upper shelf for all 60" models)
- SHELF60 LOWER (lower shelf for all 60" models)
- SHELF72 UPPER (upper shelf for all 72" models)
- SHELF72 LOWER (lower shelf for all 72" models)
- CU27TOP BSWO (22 ga. stainless steel top with 4" backsplash UHT27)
- CU32TOP BSWO (22 ga. stainless steel top with 4" backsplash UHT32)
- CU48TOP BSWO (22 ga. stainless steel top with 4" backsplash UHT48)
- CU60TOP BSWO (22 ga. stainless steel top with 4" backsplash UHT60)
  - **CU72TOP BSWO** (22 ga. stainless steel top with 4" backsplash UHT72) \*Optional accessory kits shipped separately for field installation.

# **Factory Installed Options**

- Stainless Steel Finished Back
- · Other Door Hingings





This unit is listed to UL 471, CSA 120 and NSF 7 by an approved NRTL. Consult the factory or unit data plate for approval information.



Many Traulsen models are EPA Energy Star listed. Please refer to www.energystar.gov to view the most up-to-date product listing and performance data.

Approval:



Model Specified: CSI Section 11400

### **Specifications**

#### Construction, Hardware and Insulation

Cabinet exterior front, one piece sides, and doors are constructed of 22 gauge stainless steel. Cabinet interior and door liners are constructed of anodized aluminum. The exterior cabinet back and bottom are constructed of galvanized steel.

Door self close at less than 90 degrees and also include a stay open feature at 105 degrees. Gasket profile and Santoprene® material simplify cleaning and increase overall gasket life. Both the cabinet and door(s) are insulated with an average of 2" thick high density, non-CFC, foamed in place polyurethane.

#### Refrigeration System

A balanced, rear mounted, front breathing, self-contained refrigeration system using R-134a refrigerant is provided. It features a capillary tube metering device, air-cooled hermetic compressor, a forced air evaporator coil and a non-electric condensate evaporator. An 8' cord and plug is provided. Standard operating temperature for refrigerator models is 34 to 38°F.

#### Interior

Standard interior arrangements include two (2) powder coated wire shelves per door, mounted on pilasters. These are adjustable in 1/2" increments, allowing for a minimum of 1-1/2" spacing between shelves.

#### Warranties


Both a three year parts and labor warranty and a five year compressor warranty (self-contained models only) are provided standard.


|       |                   | rigeration Data              | Shipping Data<br>(42"D x 41"H) |                            |                   |  |
|-------|-------------------|------------------------------|--------------------------------|----------------------------|-------------------|--|
| Model | Full Load<br>Amps | 4a NEMA 5-15P<br>BTU/HR - HP | Width -<br>crated              | Volume -<br>crated cu. ft. | Weight - lbs.     |  |
| UHT27 | 7.5               | 1390 (1/4)                   | 45"                            | 45                         | 240 net/275 gross |  |
| UHT32 | 7.5               | 1390 (1/4)                   | 45"                            | 45                         | 255 net/300 gross |  |
| UHT48 | 7.5               | 1390 (1/4)                   | 69"                            | 69                         | 355 net/400 gross |  |
| UHT60 | 7.5               | 1390 (1/4)                   | 69"                            | 69                         | 457 net/500 gross |  |
| UHT72 | 7.5               | 1390 (1/4)                   | 84"                            | 84                         | 548 net/575 gross |  |


#### NOTES:


- $\cdot$  Based on a 90 degree F ambient and 20 degree F evaporator.
- When ordering please specify: voltage, hinging, optional accessories and any additional warranties.
- This unit may be manufactured in other electrical characteristics and may have additional regulatory agency approvals. Consult factory for other electrical characteristics and agency approvals based on specific electrical and country requirements. (For exact electrical information and approval marks, always refer to the data label of the unit.)
- · Continued product development may necessitate specification changes without notice


| Cabinet Dimensional Data |                 |                    |                 |                          |                    |               |              |                             |  |  |  |
|--------------------------|-----------------|--------------------|-----------------|--------------------------|--------------------|---------------|--------------|-----------------------------|--|--|--|
|                          |                 | Α                  | В               | С                        |                    |               |              |                             |  |  |  |
| Model                    | Storage cu. ft. | Width -<br>cabinet | Width -<br>door | Depth - door<br>open 90° | Clear door opening | # of<br>doors | # of shelves | Total shelf<br>area sq. ft. |  |  |  |
| UHT27                    | 7.1             | 27"                | 25 7/8"         | 55 3/8"                  | 22 3/4"            | 1             | 2            | 4.88                        |  |  |  |
| UHT32                    | 8.3             | 32"                | 30 13/16"       | 60 3/8"                  | 27 3/4"            | 1             | 2            | 6.1                         |  |  |  |
| UHT48                    | 13.5            | 48"                | 21 1/8"         | 50 5/8"                  | 18"                | 2             | 4            | 10.3                        |  |  |  |
| UHT60                    | 17.4            | 60"                | 25 7/8"         | 55 3/8"                  | 22 3/4"            | 2             | 4            | 13.2                        |  |  |  |
| UHT72                    | 21.3            | 72"                | 30 13/16"       | 60 3/8"                  | 27 3/4"            | 2             | 4            | 15.5                        |  |  |  |











Part No. TR35819 (REV. 02-05-16)