

Frick Surge Drum- 25 Gallon

Mfg: Frick

Model:

Stock No. NOI8018.

Serial No.:

Frick Surge Drum- 25 Gallon. Inside straight-wall dimensions: 1 ft. 4 in. dia. x 2 ft. 8 in. L. MAWP: 150 psi @ 300°F. Hydrostatic test pressure: 400 psi. Inlets: (1) 1-1/2 in. dia. compressor suction port, (1) 1/2 in. dia. liquid feed port, (1) 3/4 in. dia. wet suction port. Outlets: (1) 3/4 in. dia. relief port, (1) 3/4 in. dia. liquid discharge port. Overall dimensions: 3 ft. 9 in. L x 2 ft. 8 in. W x 7 ft. 7 in. H.



