

Reeves Motodrive® Variable Speed Reducer – 5 HP

Mfg: Reeves

Model:

Stock No: NOI8052

Serial No: MFC40548-SF

Reeves Motodrive® Variable Speed Reducer. Serial: MFC40548-SF. Size: 332. Manually adjustable speed reducer. Reliance electric motor, 5 hp, 1710 rpm, 230/460 V, 18.4/9.2 amps, 60 Hz. 3 phase. Minimum rpm: 28. Maximum rpm: 84. Gear Ratio: 31.4:1 Overall dimensions: 2 ft. 10-1/4 in. L x 1 ft, 3-1/2 in. W x 2 ft. 2 in. H.



