

Cherry-Burrell Centrifugal Pump

Mfg: Cherry-Burrell

Model: VA

Stock No: NOIP1117

Serial No: 34329

Cherry-Burrell Centrifugal Pump. Model: VA. S/N: 34329. Sterling Electric motor: 2 hp, 1750 rpm, 208-230/460 v, 6.39-5.78/2.89 a, 60 Hz, 3 phase. (1) 5 in. dia. impeller. Inlet/outlet: (1) 2 in. ACME, (1) 1-1/2 in. ACME. Overall dimensions: 1 ft. 5-1/2 in. L x 11 in. W x 7-1/2 in. H.





STERLING for the U.S. and Canada
ELECTRIC, INC. 

IRVINE, CA 1-800-654-6220
C US LPI113663

MODEL NO. XBO024PHA	
HP 2	VOLTS 208-230/460 AMP. 6.79-5.78/2.89
F/L RPM 1750	ENCL. TEFC FRAME NO. 145TC
INS. F	MAX. AMB. 40 °C SERVICE FACTOR 1.15
3-PHASE	TIME RATING CONT. BRG. D.E. 6205
Hz 60	KVA CODE J NO. O.D.E. 6204
	EFFICIENCY 84.0% NEMA DESIGN B

LOW VOLTS	HIGH VOLTS
4 5 6	4 5 6
7 8 9	7 8 9
10 20 30	10 20 30

 **MADE IN KOREA**  S/N 040012