

APV Puma Sanitary Centrifugal PUMP

Mfg: APV

Model:

Stock No: NOIP8293

Serial No:

APV Puma Sanitary Centrifugal Pump. Capacity 85 gpm. Impeller diameter: 5-1/2 in. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. U.S. Electrical motor: 3 Hp, 1765 Rpm, 208-230/460 V, 8.6-8/4, 60 Hz, 3 Phase. Inlet: (1) 3 in. dia. ACME fitting. Outlet: (1) 2 in. dia. ACME fitting. Overall dimensions: 1 ft. 9-1/2 in. L x 1 ft. 2 in. W x 11-1/2 in. H.







MODEL T398A FR 132TD TYPE FCI ENCL TE

SHAFT END BRG 6206-2ZJC3 ORP END BRG 6205-2ZJC3

PH 3 MAX AMPS 40°C IDW 311-T398A-H

INSUL CLASS F DUTY CONT USABLE ON 208V 60HZ AT 9.8 MAX AMPS

HP 3	RPM 1765	HP 3	RPM 1450		
VOLTS 208-230/480		VOLTS 190/380			
FL AMPS 8.6-8.74		FL AMPS 9.6/4.8			
SF 1.5	DESIGN 3	CODE K	SF 1.0	DESIGN -	CODE H
NEMA NOM EFFICIENCY 87.5	NOM PF 79.3	NEMA NOM EFFICIENCY 85.5	NOM PF 83.3		
GUARANTEED EFFICIENCY 85.5	MAX KVAR 1.4	GUARANTEED EFFICIENCY 82.5	MAX KVAR 1.2		

60 HERTZ DATA

50 HERTZ DATA

U.S. ELECTRICAL MOTORS
DIVISION OF EMERSON ELECTRIC CO.
ST. LOUIS, MO
MADE IN MEXICO

EMERSON

WORLDWIDE MOTOR ENERGY EFFICIENT MOTOR

9676X