

Goolds Centrifugal Pump

Mfg: Goolds

Model: 3196

Stock No. NPPC220B.

Serial No. 723E075

Goolds Centrifugal Pump. Model: 3196. S/N: 723E075. Size: 2x3-10. 316 stainless steel. Impeller diameter: 8-1/2 in. Maximum design pressure @ 100 °F: 275 psi. Reliance Electric Motor: 7.50/3.30 hp, 1775/1185 rpm, 460/460 V, 9.40/5.50 amps, 60/60 Hz, 3 phase. Overall dimensions: 55 in. L x 20 in. W x 24 in. H.

