

MODEL	CAPACITY (BTUH/° F. TD)	AIR FLOW (CFM)	FACE VELOCITY* (FPM)	FANS		SOUND LEVEL (dbA@10')	SURFACE (FT. ²)	INTERNAL VOLUME (FT. ³)	DIMENSIONS L x D x H** (INCHES)	APPROX. WEIGHT (LBS.)
				QTY.	HP					
HP11-63-1	4,700	9,000	800	1	1	80	886	1.6	63 x 40 x 42	1,100
HP11-64-1	4,960	8,600	760	1	1	80	1,160	1.6	63 x 40 x 42	1,200
HP11-83-1	5,580	8,500	755	1	1	80	1,180	2.1	63 x 40 x 42	1,400
HP11-84-1	5,970	8,100	730	1	1	80	1,540	2.1	63 x 40 x 42	1,500
HP14-63-1	5,200	9,500	680	1	1	80	1,100	1.9	74 x 40 x 42	1,300
HP14-64-1	5,460	9,300	665	1	1	80	1,440	1.9	74 x 40 x 42	1,400
HP14-83-1	6,300	9,100	650	1	1	80	1,470	2.4	74 x 40 x 42	1,700
HP14-84-1	6,580	8,660	620	1	1	80	1,920	2.4	74 x 40 x 42	1,800
HP14-63-1½	6,100	11,500	820	1	1½	80	1,100	1.9	74 x 40 x 42	1,300
HP14-64-1½	6,500	11,100	790	1	1½	80	1,440	1.9	74 x 40 x 42	1,400
HP14-83-1½	7,100	11,100	790	1	1½	80	1,470	2.4	74 x 40 x 42	1,700
HP14-84-1½	7,500	10,600	760	1	1½	80	1,920	2.4	74 x 40 x 42	1,800
HP23-63-1	9,400	18,000	800	2	1	83	1,770	2.7	108 x 40 x 42	1,900
HP23-64-1	9,920	17,200	760	2	1	83	2,310	2.7	108 x 40 x 42	2,000
HP23-83-1	11,160	17,000	755	2	1	83	2,360	3.6	108 x 40 x 42	2,200
HP23-84-1	11,940	16,200	730	2	1	83	3,080	3.6	108 x 40 x 42	2,400
HP28-63-1	10,400	19,000	680	2	1	83	2,200	3.3	130 x 40 x 42	2,200
HP28-64-1	10,920	18,000	665	2	1	83	2,880	3.3	130 x 40 x 42	2,400
HP28-83-1	12,600	18,200	650	2	1	83	2,940	4.3	130 x 40 x 42	2,700
HP28-84-1	13,160	17,320	620	2	1	83	3,830	4.3	130 x 40 x 42	2,900
HP28-63-1½	12,200	23,000	820	2	1½	83	2,200	3.3	130 x 40 x 42	2,200
HP28-64-1½	13,000	22,100	790	2	1½	83	2,880	3.3	130 x 40 x 42	2,400
HP28-83-1½	14,200	22,100	790	2	1½	83	2,940	4.3	130 x 40 x 42	2,700
HP28-84-1½	15,000	21,300	760	2	1½	83	3,830	4.3	130 x 40 x 42	2,900