

Reliance Electric Agitator Drive

Mfg: Reliance

Model:

Stock No. OI165.

Serial No.

Reliance Electric Agitator Drive. Gear driven for maximum torque output. Reliance Electric Motor, 5/2.5 Hp, 1,725/860 rpm, 230 V, 60 Hz, 3 phases. Motor drive, 101 ratio, 17/8.5 rpm (final). Shaft dimensions: 2-1/2 in W x 6 in L. Mount base has a 16-1/2 in. dia. flange with (8) 1/2 in. dia. attachment holes at a center-to-center distance of 15-1/2 in. Overall dimensions: 44 in. L x 18 in. W x 22 in. H.

