

Wolfking Vertical Screw Auger Conveyor

Mfg: Wolfking

Model: Vertical

Stock No. OI203.

Serial No. 5846

Wolfking Vertical Screw Auger Conveyor. Model: Vertical. S/N: 5846. Auger: 8-1/2 in. dia. x 73 in. H. Discharge offset 90°. Lincoln Motor, 15 hp, 1750 rpm, 230/460 V, 10/.20 amps, 60 Hz, 3 phase. The vertical screw conveyors are designed for transport of pre-ground material where the space is limited. Exit height: 67-1/2 in. (4) adjustable wheels for easy maneuverability. Inlets: (1) 10 in dia. port. Outlets: (1) 15 in. L x 13-1/2 in. W discharge. Overall dimensions: 54 in. L x 48-1/2 in. W x 91-1/2 in. H.





