

Brooks Wafer-Mag Magnetic Flowmeter

Mfg: Brooks

Model: 7401C1W1C1AA

Stock No. OI212.

Serial No. 8903-12114

Brooks Wafer-Mag Magnetic Flowmeter. Model: 7401C1W1C1AA. S/N: 8903-12114. K-Factor: 7857.069PPG. Maximum process pressure: 740 psi @ 100 °F. Maximum process temperature: 300 °F. Power requirements: 115 VAC, 50/60 Hz. Flowtube inlets/outlets: (2) 1 in. dia. lapped flanges. Overall dimensions: 12 in. L x 7 in. W x 11 in. H.



