

## Screw Auger

**Mfg: Not Specified**

**Model:**

**Stock No: OI234.**

**Serial No:**

Screw Auger. Screw auger dimensions: 18 in. dia. x 12 ft. 7 in. L. (2) Toshiba Motors, 10 hp, 1170 rpm, 230/460 V, 28.4/14.2 amps, 60 Hz, 3 phase. U.S. Syncro Gear Motor (auger), 2 hp, 1800 rpm, 220-440 V, 60 Hz, Gear ratio: 26.7, Final rpm: 66. Infeed height: 69 in. Outlets: 19 in. L x 15 in. W discharge. Overall dimensions: 13 ft. 9 in. L x 5ft. 6 in. W x 5ft. 9 in. H.



