

Stainless Steel Centrifugal Deaerator Skid

Mfg: N/A

Model: N/A

Stock No.: OI244

Serial No.: N/A

Stainless Steel Centrifugal Deaerator Skid. Maximum tank volume: 8 gal. Mixing head diameter: 7-1/2 in. Mixer Motor, 3/4 hp, 220 V, 2.25 amps, 60 Hz, 3 phase. Fryma-Maschinen Progressing Cavity Positive Displacement Pump, Model: NU-15A. Motor, 1/2 hp, 1100 rpm, 380 V, 1.4 amps, 60 Hz, 3 phase. Siemen and Hirsch Vacuum Pump with Motor, Model: LEMA 25 A7 GA1 7C0, S/N: D-3126498. Inlets: (1) 3/8 in. dia. vacuum port, (1) 1/2 in. dia. MPT, (1) 1 in. dia. flanged port. Outlets: (1) 1-1/2 in. dia. port. Overall dimensions: 54 in. L x 22 in. W x 52 in. H.



