

Mix and Blend Tank, 100 gallon, sloped cone bottom. Reliance Motor, ID No. P14H3598N-SS, Frame F0145TC, Type C, 2 hp, 3,450 rpm, 208/230 volt, 6.4/6.4 amps, 60 hz, 3 phase. APV Crepaco Pump, S/N E-D879-6V-86, 1/2 in. outlet from pipe to T joint also connecting with the bottom of the tank. Inside dimensions 30 in. diameter x 45 in. H, (4) 19 in. legs with wheels, overall dimensions 50 in. L x 34 in. W x 63-1/2 in. H.

