

## Table Top Conveyor

**Mfg:**

**Model:**

**Stock No: OI52**

**Serial No:**

Table Top Conveyor. (2) Pulleys: driver dia. 3-1/2 in. and driven dia. 4-1/2 in. Reliance Electric motor: 1/2 hp, 1725 rpm, 208-230/460-480 V, 2.4-2.4/ 1.2-1.4 A, 60 Hz, 3 phase. Dodge Tigear drive: max input hp: 0.58, input rpm: 1750, output torque: 6.39. Belt dimensions: 140 in. L x 7-1/2 in. W. Overall dimensions: 12 ft. L x 2 ft. W x 2 ft. 10-3/4 in. H.



