

Goulds Centrifugal Pump




Mfg: Goulds

Model: 3196

Stock No. OIP040.

Serial No. 707E722

Goulds Centrifugal Pump. Model: 3196. S/N: 707E722. Size: 2x3-10. 316 stainless steel. Maximum design pressure @ 100 °F: 275 psi. Impeller diameter: 9 in. Double mechanical seals with water flush. Reliance Electric Motor: 7.5/3.30 hp, 1775/1185 rpm, 460/460 V, 9.40/5.50 amps, 60/60 Hz, 3 phase. Overall dimensions: 55 in. L x 20 in. W x 26 in. H.



Goolds Centrifugal Pump Curve

