

Goulds Centrifugal Pump

Mfg: Goulds

Model: 3196

Stock No. OIP041.

Serial No. 756E317

Goulds Centrifugal Pump. Model: 3196. S/N: 756E317. 316 stainless steel. Impeller diameter: 8-1/2 in. Double mechanical seals with water flush. Reliance Electric Motor: 7.5/3.30 hp, 1775/1185 rpm, 460/460 V, 9.40/5.50 amps, 60/60 Hz, 3 phase. Overall dimensions: 55 in. L x 20 in. W x 23 in. H.

